

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

532nm 0 - 250mW, Fiber-Coupled Laser



Fiber-Coupled Laser System

Stock #33-048 CLEARANCE 3-4 DAYS



1



€6.315,95

ADD TO CART

Qty 1+

€6.315,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):

+10 to +30

Output Power (mW):

250 (Maximum)

Dimensions (mm):

76.2 L x 152.4 W x 254.0 H

Fiber Diameter (µm):

400.00

Wavelength (nm):

532.00
Weight (kg): 1.13
Wavelength Tolerance (nm): ±5
Operating Humidity: 5 to 95%, non-condensing
Length of Cable (m): 0.5
Cooling Method: TE Cooled with forced air
Beam Divergence (NA): 0.22, Nominal
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Green
Connector: SMA
Input Voltage (V): 100 - 240 AC
Bandwidth (nm): <3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View