

[See all 2 Products in Family](#)

## 23 x 20mm FL, Grade 1, Double-Convex Lens



Stock #74-324 CLEARANCE **3 In Stock**

€10<sup>25</sup>

ADD TO CART

Volume Pricing	
Qty 1+	€10,25 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

**Diameter (mm):**  
23.00

### Optical Properties

**Effective Focal Length EFL (mm):**  
20.00

### Regulatory Compliance

**Certificate of Conformance:**

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

50mm and Larger Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

