

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

LightPath 354260 | 543nm Alignment, 0.16 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



543nm Alignment, 0.16 NA Fiber Collimator w/ FC Connector, #47-224

Stock #47-224 3-4 DAYS



1



€180,00

ADD TO CART

Qty 1-10

€180,00

Qty 11+

€158,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
15.29 @ 780nm

Numerical Aperture NA:
0.16

Substrate:

Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.00
f#: 3.13
Bevel: Protective bevel as needed
Connector: FC/PC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 20.2
Lightpath Lens Code: 354260
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Lens Included: #37-098
Alignment Wavelength (nm): 543

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
