

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Fiber Optic Collimator and Focuser Assemblies



Stock #64-786 3-4 DAYS



1



€180,00

ADD TO CART

Qty 1-10

€180,00

Qty 11+

€158,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
4.51 @ 780nm

Numerical Aperture NA:
0.55

Substrate: D-ZLaF52LA
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 4.95
f#: 0.91
Bevel: Protective bevel as needed
Connector: SMA
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 9.6
Lightpath Lens Code: 355230
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Lens Included: #87-153
Alignment Wavelength (nm): 543

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant