

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

5.6" Diagonal LCD Flat Panel Monitor



Stock #55-786 CLEARANCE 3-4 DAYS

- 1 +

€149,95

ADD TO CART

Qty 1+

€149,95

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Monitor

Resolution (MegaPixels):
0.20

Pixels (H x V):
960 x 234

Power Supply:
100 - 240 VAC Included

Power Consumption (W):
<7

Dimensions (mm): 133 W x 160 H x 37 D
Dot Pitch (mm): 0.119 x 0.357
Size of Screen, Diagonal (inches): 5.6
Maximum Viewing Angle, MVA (°): 45 Left/Right, 10 Up/Down
Weight (kg): 0.458
Input/Output Options: Mini Phone Jack (RCA Adapter Included)/ No Output Terminals
Active Area (mm): 113.3 H x 84.7 W
Signal Format: NTSC/ PAL
Contrast: 150:1
Brightness (cd/m²): 200
Response Time (ms): 35
Safety Standards: FCC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View