

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

5.6mm FL, High Resolution, 1/2, Micro Video Lens



Stock #88-592 3-4 DAYS

- 1 + €74,00

ADD TO CART

Qty 1-49

€74,00

Qty 50+

€57,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
22.20

Maximum Diameter (mm):
17.0

Maximum Image Circle (mm):
6.50

Horizontal Field of View @ Max Sensor Format:

50
Resolution, On-Axis: 100 lp/mm @67.0% Contrast
Resolution, 0.7 Field: 100 lp/mm @51.0% Contrast
Resolution, Full Field: 100 lp/mm @49.2% Contrast
Note: High Resolution
TV Distortion (%): -1.5
Type: M12 Imaging Lens
Focal Length FL (mm): 5.60
Maximum Sensor Format: 1/2.8"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View