

# 590nm, Coaxial LED Spot Light

See More by [Advanced Illumination](#)



Stock **#66-864** 3-4 DAYS

⊖ 1 ⊕ **€507,00**

ADD TO CART

Qty 1+

€507,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Color:**  
Yellow

**Model Number:**  
SL112-590-IC

**Operating Temperature (°C):**  
0 to 60

**Wavelength (nm):**

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 590.00                                                                                                                                                                                                                                      |
| <b>Weight (g):</b><br>42.5                                                                                                                                                                                                                  |
| <b>LED Lifetime (hours):</b><br>50,000                                                                                                                                                                                                      |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Light Distribution (%):</b><br>±10                                                                                                                                                                                                       |
| <b>Number of LEDs:</b><br>1 High Brightness                                                                                                                                                                                                 |
| <b>Length of Cable (m):</b><br>1.5                                                                                                                                                                                                          |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Spot Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Constant                                                                                                                                                                                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |