

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 5mm Dia., 2mm Thick, VIS-NIR Coated M4 N-BK7 Window



Stock #48-448 3-4 DAYS



1



€79,00

ADD TO CART

Qty 1-5

€79,00

Qty 6+

€63,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm): 4.50
Diameter (mm): 5.00 +0.0/-0.25
Thickness (mm): 2.00 ±0.20
Coating: VIS-NIR (400-1000nm)
Coating Specification: R_{abs} ≤0.25% @ 880nm R_{avg} ≤1.25% @ 400 - 870 nm R_{avg} ≤1.25% @ 890 - 1000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 400 - 1000
Young's Modulus (GPa): 82
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant