

[See all 57 Products in Family](#)

TECHSPEC[®]

5mm Diameter, C-Mount Thick Optic Mount



Stock **#57-974** 6 In Stock

-

1

+

€59⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€59,50 each
Qty 5-9	€56,90 each
Qty 10-25	€55,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:	
Fixed	
Type of Optics:	
Circular	
Function:	

Physical & Mechanical Properties

14.0 Extension Length (mm):

Black Anodized Aluminum (6061 T6) Construction:

18.0 Total Length (mm):

30.0 Outer Diameter (mm):

3.00 Clear Aperture CA (mm):

6.5 Max. Thickness of Compatible Optics (mm):

1.0 Min. Thickness of Compatible Optics (mm):

Threading & Mounting

5.0 Diameter of Compatible Optics (mm):

C-Mount Thread Type:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant REACH 241:

Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

Technical Information

