

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

5" X 5" , 4" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock #46-614 ■ In Stock



1



€89,00

ADD TO CART

Qty 1-10

€89,00

Qty 11+

€78,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
101.60

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 5.0 x 5.0
Dimensions (mm): 127.0 x 127.0
Effective Diameter (inches): 4.0
Effective Focal Length EFL (inches): 4.00
Groove Density (grooves/inch): 100.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View