

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

5X Nikon CF160 TU Plan Epi Infinity Corrected Obj

See More by [Nikon](#)



#58-515: 5XNikon CF160 TU Plan Epi

Stock #58-515 3-4 DAYS



1



€944,00

ADD TO CART

Qty 1+

€944,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
4.40

Horizontal Field of View, 1/2" Sensor:
1.28mm

Horizontal Field of View, 2/3" Sensor:
1.76mm

Focal Length FL (mm):
40.00

Model Number: MJE12050
Length excluding Threads (mm): 36.30
Magnification: 5X
Maximum Diameter (mm): 29
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.15
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 2.0
Depth of Field (µm): 12.22
Field of View, 25 Diameter Field Eyepiece (mm): 5.00
Field of View, 22 Diameter Field Eyepiece (mm): 4.4
Working Distance (mm): 23.5
Weight (g): 100.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 60
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View