

TECHSPEC® 6" Diameter x 24" FL Protected Aluminum, Parabolic Mirror



Stock #32-069-522 3-4 DAYS

⊖ 1 ⊕ **€681,00**

ADD TO CART

Qty 1-4
€681,00
Qty 5+
€579,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±1

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 6.0 +0.06/-0
Diameter (mm): 152.40 +1.5/-0
Effective Focal Length EFL (inches): 24.0
Effective Focal Length EFL (mm): 609.60
Radius of Curvature (mm): 1,219.20
Aperture (f/#): f/4
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 138
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference:  0.3 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant