

6 Watt, 230V, 365nm UV Curing Lamp



6 Watt, 230V, 365nm UV Curing Lamp, #86-805

Stock **#86-805** CLEARANCE **3 In Stock**

€350⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€350,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Voltage converter required for use in U.S.

Optical Properties

Wavelength (nm):
365.00

Irradiance at 76.2mm (μW/cm²):
2300

Hardware & Interface Connectivity

6W, 230V

Power Requirement:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

Stands are not included, but recommended for hands free curing or analysis.

- 4-Watt and 6-Watt Models Centered at 365nm
- Stands are Available for Hands Free Curing
- Portable, High Intensity Design

Handheld UV Curing Lamps are portable benchtop lamps designed for a variety of applications including the fluorescence of stained gels, sterilization, or UV curing. These lamps feature ergonomically designed handles with conveniently placed on/off switches. These lamps are portable, with a high-intensity design. Handheld UV Curing Lamps are ideal for quickly curing Edmund Optics' full line of [Norland Optical Adhesives](#). These lamps are available in 4-watt and 6-watt models centered at 365nm.

Note: Stands are not included, but are recommended for hands free curing or analysis.
