

## 60 x 35mm English Base Plate



Stock #58-997 **10 In Stock**

⊖ 1 ⊕ €30<sup>75</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€30,75 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English **Type:**

### Physical & Mechanical Properties

60.00 **Length (mm):**

35.00 **Width (mm):**

7.00 **Thickness (mm):**

Black Anodized Aluminum **Construction:**

2 **Number of Slots:**

## Threading & Mounting

(4) 8-32, (5) 1/4-20 **Mounting Threads:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 250:**

## Product Details

- Two Size Options
- Two Platform Options: English or Metric
- English: Four #8-32 holes on 1/2" Square and Four 1/4-20 Holes on 1" Square
- Metric: Four M4 x 0.7 holes on 12.5mm Square and Four M6 x 1 Holes on 25mm Square
- Anodized Aluminum Construction

Base Plates have Metric or English threaded holes and additional center trapped hole (M6 x 1 or 1/4-20). Base Plates also have extended center slots that ensure full use on matching metric or English breadboard patterns. 85mm x 50mm Base Plates have same tapped holes and slots as 60mm x 35mm Base Plates, but with extra short slots for added flexibility.

## Technical Information

