

60 x 35mm English Base Plate



Stock **#58-997** 10 In Stock

-

1

+

€30^{,75}

ADD TO CART

Volume Pricing	
Qty 1+	€30,75 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

English

Physical & Mechanical Properties

Length (mm):

60.00

Width (mm):

35.00

Thickness (mm):

7.00

Black Anodized Aluminum	Construction:
2	Number of Slots:
Threading & Mounting	
(4) 8-32, (5) ¼-20	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Two Size Options
 - Two Platform Options: English or Metric
 - English: Four #8-32 holes on ½" Square and Four ¼-20 Holes on 1" Square
 - Metric: Four M4 x0.7 holes on 12.5mm Square and Four M6 x1 Holes on 25mm Square
 - Anodized Aluminum Construction
- Base Plates have Metric or English threaded holes and additional center trapped hole (M6 x 1 or ¼-20). Base Plates also have extended center slots that ensure full use on matching metric or English breadboard patterns. 85mm x 50mm Base Plates have same tapped holes and slots as 60mm x 35mm Base Plates, but with extra short slots for added flexibility.

Technical Information

