

600 Grooves, 25mm Square, 1250nm NIR Ruled Grating



Stock #49-574 **5 In Stock**

- 1 + €185⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€185,00 each
Qty 10-24	€166,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Reflective Diffraction Grating **Type:**

Physical & Mechanical Properties

25.0 x 25.0 ±0.5 **Dimensions (mm):**

90 **Clear Aperture (%):**

Ruled Grating	Construction:
Parallel to Short Dimension	Direction of Grooves:
25.00	Length (mm):
9.50 ±0.5	Thickness (mm):
25.00	Width (mm):
±0.5	Alignment of Grooves to Edge (°):

Optical Properties

600	Groove Density (grooves/mm):
700 - 3000	Wavelength Range (nm):
1250	Blaze Wavelength (nm):
22.02	Blaze Angle (°):
Bare Gold	Coating:
Float Glass	Substrate: <input type="checkbox"/>

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:



Product Details

- Increased Reflection from 700 - 1100nm

Near-IR (NIR) Reflective Gold Gratings are ruled gold-coated versions of our commercial gratings. These gratings provide increased reflection from 700 - 1100nm. This makes them an excellent choice for applications such as fiber optic pulse compression and spectroscopy setups using [silicon detectors](#). Near-IR (NIR) Reflective Gold Gratings feature a float glass substrate and a ruled grating construction. The gratings are available in three sizes, with varying groove densities and blaze wavelengths.

Handling Gratings: Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;