

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

600 Grooves/mm, 50mm Sq, UV Transmission Grating Beamsplitter



Stock #85-297 3-4 DAYS



1



€330,00

ADD TO CART

Qty 1-9

€330,00

Qty 10+

€297,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
600

Wavelength Range (nm):
250 - 600

Blaze Angle (°):
22.0

Dimensions (mm): 50.00 x 50.00
Construction: Blazed Grating
Length (mm): 50.00
Substrate: Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View