

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #14-341 3-4 DAYS



1



€305,00

ADD TO CART

Qty 1-5

€305,00

Qty 6+

€268,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Extinction Ratio:
9000:1

Substrate: ☐
[XP42-200 on PMMA](#)

Length (mm):
450.00

Operating Temperature (°C):

-40 to +80

Dimensions (mm):
600.0 x 450.0 +0.0/-3.0

Thickness (mm):
2.22 ±0.25

Transmission (%):
Single: 42
Parallel: 36
Crossed: <0.004

Type:
Linear Polarizer

Construction:
Polarizing Film on PMMA

Wavelength Range (nm):
400 - 700

Polarization Efficiency (%):
>99.98

Width (mm):
600.00

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)