

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

60° Diffusing Angle 50mm Dia Mounted



Stock #54-505 3-4 DAYS



1



€257,50

ADD TO CART

Qty 1-5

€257,50

Qty 6+

€219,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±6

Diffusing Angle (°):
60 (FWHM)

Clear Aperture CA (mm):
45.7

Diameter (mm):

50.00 ±0.1
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant