

6.0X Coaxial Zoom Lens, 0.37X - 2.23X Range



6.0X Coaxial Zoom Lens, 0.37X - 2.23X Range, #83-895

Stock **#83-895** 3-4 DAYS

- 1 + **€2.355,00**

ADD TO CART

Qty 1+

€2.355,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
17.3 - 2.9mm

Numerical Aperture NA:
0.04 - 0.043

Weight (g):
680.00

Zoom Ratio:
6:1

Type:

Zoom Lens
Primary Magnification PMAG: 0.37X- 2.23X
Maximum Sensor Format: 1/2"
Working Distance (mm): 195.00
Mount: C-Mount
Style: In-Line Illumination
Distortion (%): 0.79 @ Min FOV, 1/2" Sensor 0.26 @ Max FOV, 1/2" Sensor
Depth of Field (mm): 10.0 - 0.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View