

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



60X Nikon Achromatic Finite Conjugate Objective

Stock #59-937 3-4 DAYS



1



€234,00

ADD TO CART

Qty 1+

€234,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Effective Focal Length EFL (mm):
2.87

Field of View (mm):
0.30

Model Number:
MSB50600

Magnification: 60X
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.80
Mounting Threads: RMS / 20.32mm x36 TPI
Type: Achromatic, Spring Loaded Head
Resolving Power (µm): 0.3
Depth of Field (µm): 0.30
Working Distance (mm): 0.24
Style: Finite Conjugate
Manufacturer: Nikon
Field Number (mm): 18
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View