

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



#66-871: 625nm, Large Diffuse LED Light

Stock #66-871 [CONTACT US](#)



1



€3.024,00

ADD TO CART

Qty 1+

€3.024,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Model Number:
DL071-625-IC

Operating Temperature (°C):
0 to 60

Wavelength (nm): 625.00
Weight (lbs): 14.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10
Number of LEDs: 24 High Brightness
Length of Cable (m): 1.5
Field Coverage (mm): 457.2 x 457.2
Maximum Trigger Frequency (Hz): 30.00
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Diffuse
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)