

630nm LED Spot Light



Stock **#63-337** 3-4 DAYS

⊖ 1 ⊕

€525,00

ADD TO CART

Qty 1+

€525,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Red

Diameter (mm):
35.00

Full Width-Half Max FWHM (nm):
30.00

Height (mm):
29.5

Mounting Threads:
M3

Wavelength (nm): 630.00
LED Lifetime (hours): 100,000
Power Supply: Power Supply Required and Sold Separately: USA: #59-433 Europe: Not Available Japan: #59-433 Korea: Not Available China: #59-433
Spot Size at 50mm Working Distance (mm): 10.00
Irradiance at 50mm (W/m²): 1000.00
Type of Illumination: LED Illuminator
Geometry: Spot Light
Maximum Input Current: 400mA
Illumination Mode: Strobed or Constant

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
