

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC High Energy Laser Line Polarizers

Stock #21-891 CLEARANCE 3-4 DAYS



1



€575,95

ADD TO CART

Qty 1+

€575,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45±2

Clear Aperture (%):
90

Clear Aperture CA (mm):
45.00

Construction:
Thin Film Dielectric

Design Wavelength DWL (nm): 633
Diameter (mm): 50.00
Dimensional Tolerance (mm): +0.00/-0.25
Extinction Ratio: 10,000:1
P-Polarization Transmission (%): >98
S-Polarization Reflection (%): >99
Substrate: Fused Silica
Surface Quality: 40-20
Thickness (mm): 6.00
Thickness Tolerance (mm): ±0.25
Transmitted Wavefront, P-V: λ/4 @ 633nm
Type: Plate Beamsplitter
Damage Threshold, By Design: 2 J/cm² @ 532nm, 10ns, S or P Polarization

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View