

37mm Max. Aperture, Mounted Stainless Steel Iris Diaphragm



Stock #62-659 [CONTACT US](#)

-

1

+

€138,00

ADD TO CART

Qty 1-4
€138,00

Qty 5+
€121,40

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type: Mounted
Minimum Aperture (mm): 1.6
Maximum Aperture (mm): 37.0
Outer Diameter (mm):

66.0
Construction: Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators
Lever Diameter (mm): 3.00
Lever Length (mm): 12.50
Number of Leaves: 16.00
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)
