

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

6.7" X 6.7" , 5" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock #32-593 ☒ In Stock



1



€106,00

ADD TO CART

Qty 1-10

€106,00

Qty 11+

€93,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
76.20

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 6.7 x 6.7
Dimensions (mm): 170.18 x 170.18
Effective Diameter (inches): 6.0
Effective Focal Length EFL (inches): 3.00
Groove Density (grooves/inch): 100.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View