

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Zero Series

Stock #57-591 3-4 DAYS



1



€175,00

ADD TO CART

Qty 1-4

€175,00

Qty 5+

€154,70

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Aperture (mm):  
0.00

Maximum Aperture (mm):  
40.0

Outer Diameter (mm):  
69.0

|                                                                   |
|-------------------------------------------------------------------|
| <b>Construction:</b><br>Anodized Aluminum Alloy, Burnished Leaves |
| <b>Full Angular Range of Lever (°):</b><br>96.00                  |
| <b>Lever Length (mm):</b><br>16.00                                |
| <b>Lever Position (mm):</b><br>3.3                                |
| <b>Lever Size (mm):</b><br>6.00 x 1.50                            |
| <b>Number of Leaves:</b><br>Two sets of 7                         |
| <b>Operating Temperature (°C):</b><br><250                        |
| <b>Pin Thread &amp; Pitch:</b><br>N/A                             |
| <b>Thickness (mm):</b><br>6.50                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |