

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 6mm Dia X 12mm FL MgF₂ Coated, Illumination Grade PCX Cylinder Lens



Stock #68-040 [CONTACT US](#)

- 1 + **€70,50**

ADD TO CART

Qty 1-5

€70,50

Qty 6+

€56,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
12.00

Substrate: ☐
[N-BK7](#)

f/#: 2
Numerical Aperture NA: 0.25
Coating: MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): 10.55
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.43
Focal Length Tolerance (%): ±3
Radius R ₁ (mm): 6.20
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant