

TECHSPEC® 6mm Dia x 6mm FL MgF₂ Coated, Illumination Grade PCX Cylinder Lens



Stock **#68-038** 3-4 DAYS

⊖ 1 ⊕ **€70,50**

ADD TO CART

Qty 1-5
€70,50
Qty 6+
€56,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
6.00

Substrate: ☐
[N-SF11](#)

f/#: 1
Numerical Aperture NA: 0.5
Coating: MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): 4.55
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.52
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 4.71
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View