

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



65mm WD, 6X, In-Line Version (Left) and VIS Version (Right)

Stock #63-743 3-4 DAYS



1



€672,00

ADD TO CART

Qty 1+

€672,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
116.10

Horizontal Field of View, 1/2" Sensor:
1.1mm

Horizontal Field of View, 2/3" Sensor:
1.5mm

Filter Thread:
M25.5 x0.50 (Female) with Required Adapter [#88-212](#)
Sold Separately

Maximum Diameter (mm): 18.00
Weight (g): 58
Horizontal Field of View, 1/3" Sensor: 0.8mm
Numerical Aperture NA, Object Side: 0.085
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 5 (3)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.072
Typical Distortion @ 588nm (%): 0.019
Front Thread: M17 x 0.5 (Female)
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 6X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65
Mount: C-Mount
Aperture (f/#): f/35
Coating: λ/4 MgF ₂
Depth of Field (mm): ±0.05mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 1.5 x 1.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View