

700mm Neck, Flood Lamp



Stock **#58-077** [CONTACT US](#)

-

1

+

€167^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€167,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type of Illumination:

Fiber Optic Illuminator, Incandescent

Geometry:

Spot Light

Illumination Mode:

Constant

Optical Properties

Color:

White

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

Gooseneck quartz halogen illuminators feature a 12V/20W Halogen bulb housed in a high impact, polyamide housing. A heat dissipating Dichroic reflector and clear lens provide a wide angle illumination (flood) or a narrow spot. The lamphead is mounted on a 700 or 500mm gooseneck arm that easily adjusts to any angle. Lamps can be secured directly to a bench or can be mounted on a table top base or an adjustable C-clamp, listed below.

;