

TECHSPEC® 70mm, 120mm Radius, English Goniometer



TECHSPEC® Goniometers



Stock **#66-532** [CONTACT US](#)

- 1 + **€689,00**

ADD TO CART

Qty 1-2

€689,00

Qty 3+

€600,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: English
Stage Size (mm): 70 x 70
Travel (°): ±10
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 6
Mounting Threads: (9) 1/4-20, (4) 6-32, (8) 2-56
Radius R (mm): 120
Resolution (arcmin): 5
Stage Size (inches): 2.75 x 2.75
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant