

**TECHSPEC® 70mm, Center Drive, Standard Top, English Extended Micrometer**



#66-427 - 70mm, 0.5" Travel, Micrometer Drive Stage (Center Drive)

Stock **#66-428** 3-4 DAYS



1



€487,00

ADD TO CART

Qty 1-2

€487,00

Qty 3+

€425,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Crossed Roller Bearing

Type of Drive:  
English Micrometer

|                                                            |
|------------------------------------------------------------|
| <b>Drive Orientation:</b><br>Center Drive                  |
| <b>Type:</b><br>English                                    |
| <b>Stage Size (mm):</b><br>70 x 70                         |
| <b>Travel (inches):</b><br>1                               |
| <b>Center Hole:</b><br>1/4-20                              |
| <b>Construction:</b><br>Aluminium Stage                    |
| <b>Leadscrew Pitch (mm):</b><br>0.635                      |
| <b>Load Capacity (kg):</b><br>8                            |
| <b>Mounting Threads:</b><br>(8) 1/4-20, (4) 6-32, (8) 2-56 |
| <b>Stage Size (inches):</b><br>2.75 x 2.75                 |
| <b>Straight Line Accuracy (µm):</b><br>2                   |
| <b>Pitch (arcsec):</b><br>30                               |
| <b>Yaw (arcsec):</b><br>25                                 |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |