

## 50mm Max. Aperture, Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock #57-584 3-4 DAYS



1



€178,00

ADD TO CART

Qty 1-4

€178,00

Qty 5+

€157,40

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Unmounted

Minimum Aperture (mm):  
2.5, Typical

Maximum Aperture (mm):  
50.0

|                                                                         |
|-------------------------------------------------------------------------|
| Outer Diameter (mm):<br>70.0                                            |
| Construction:<br>Anodized Aluminum Alloy, Burnished Spring Steel Leaves |
| Lever Diameter (mm):<br>3.00                                            |
| Lever Length (mm):<br>15.00                                             |
| Number of Leaves:<br>18.00                                              |
| Thickness (mm):<br>7.00                                                 |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |
| Reach 240:<br><a href="#">Compliant</a>             |