

TECHSPEC® 70mm, Side Drive, Thru-Hole, Metric Micrometer Stage



Stock #66-448 3-4 DAYS

⊖ 1 ⊕ **€468,00**

ADD TO CART

Qty 1-2
€468,00
Qty 3+
€408,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Metric Micrometer

Drive Orientation:

Side Drive
Type: Metric
Stage Size (mm): 70 x 70
Travel (mm): 13
Center Hole: 1" x 32 TPI
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 8
Mounting Threads: (1) 1" x 32, (7) M6 x 1, (4) M3 x 0.5
Stage Size (inches): 2.75 x 2.75
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
