

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 725nm 12.5mm Diameter, OD 4.0 Shortpass Filter



High Performance OD 4.0 Shortpass Filters

Stock #86-095 [CONTACT US](#)



1



€199,00

ADD TO CART

Qty 1-5

€199,00

Qty 6+

€159,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Cut-Off Wavelength (nm): 725.00
Substrate: Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 740 - 1090
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.1
Transmission (%): ≥91
Transmission Wavelength (nm): 400 - 710
Type: Shortpass Filter
Clear Aperture (%): >80
Transmitted Wavefront, RMS: ≤λ/4 @ 633nm (prior to coating)
Slope Factor (%): <1
Cut-Off Tolerance (%): ±1
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Note: Arrow on part indicates filter coated surface.
Wavelength Range (nm): 400 - 1090

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant