

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 75 X 75mm Enhanced Aluminum Coated, λ/10 ZERODUR® Mirror



TECHSPEC ZERODUR λ/10 First Surface Mirrors

Stock #17-797 3-4 DAYS



1



€455,00

ADD TO CART

Qty 1-5
€455,00

Qty 6+
€363,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate:
ZERODUR®

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 75.0 x 75.0 +0.00/-0.20
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 7.50 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 75.00
Width (mm): 75.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference:  0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant