

7.50µm CWL, 25.0mm Diameter, 0.50µm FWHM, IR Bandpass Filter



Stock #17-247 3-4 DAYS

⊖ 1 ⊕ **€597,00**

ADD TO CART

Qty 1-9
€597,00
Qty 10+
€537,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):

20.0
Center Wavelength CWL (nm): 7,500.00 ±75
Full Width-Half Max FWHM (nm): 500.00 ±50
Substrate: □ Silicon Floatzone (SiFz)
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): ≥65 (at peak)
Type: Bandpass Filter
Typical Applications: Atmospheric/Solar Imaging
Blocking Wavelength Range (nm): 200 - 16000
Center Wavelength CWL (μm): 7.50 ±0.075
Full Width-Half Max FWHM (μm): 0.50 ±0.05

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View