

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC ZERODUR X10 First Surface Mirrors

Stock #17-793 3-4 DAYS



1



€455,00

ADD TO CART

Qty 1-5

€455,00

Qty 6+

€363,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
75.00 +0.00/-0.20

Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate:

Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 7.50 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant