

7.5mm Dia. x 6.6mm FL, Aspheric Condenser Lens



Stock **#19-509** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€34,00**

ADD TO CART

Qty 1-10
€34,00

Qty 11+
€31,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
7.50 +0.0/-0.2

Effective Focal Length EFL (mm):
6.60

Numerical Aperture NA:
0.57

Back Focal Length BFL (mm): 4.3
Substrate: ☐ H-K51
Focal Length Tolerance (%): ±5
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 6.75
Edge Thickness ET (mm): 1.18
Center Thickness CT (mm): 3.50 ±0.30
f/#: 0.88
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 7.5
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View