

# 76.2mm Dia. x 500mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF<sub>2</sub>) DCX Lens | CF-BX-76-500

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock #24-777 3-4 DAYS

- 1 + **€795,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €795,00                       |
| Qty 10+                       |
| €715,50                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
76.20 +0.00/-0.13

Effective Focal Length EFL (mm):

|                                                                                                  |
|--------------------------------------------------------------------------------------------------|
| 500.00 @5μm                                                                                      |
| <b>Coating:</b><br>Uncoated                                                                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Calcium Fluoride (CaF<sub>2</sub>)</a> |
| <b>Surface Quality:</b><br>60-40                                                                 |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ                                                        |
| <b>Centering (arcmin):</b><br><3                                                                 |
| <b>Bevel:</b><br>Protective bevel as needed                                                      |
| <b>Center Thickness CT (mm):</b><br>6.70 ±0.20                                                   |
| <b>Edge Thickness ET (mm):</b><br>3.00                                                           |
| <b>Radius R<sub>1</sub> (mm):</b><br>398.10                                                      |
| <b>Radius R<sub>2</sub> (mm):</b><br>398.1                                                       |
| <b>Clear Aperture CA (mm):</b><br>68.58                                                          |
| <b>f/#:</b><br>6.56                                                                              |
| <b>Focal Length Tolerance (%):</b><br>±2                                                         |
| <b>Numerical Aperture NA:</b><br>0.08                                                            |
| <b>Type:</b><br>Double-Convex Lens                                                               |
| <b>Wavelength Range (nm):</b><br>300 - 8000                                                      |
| <b>Model Number:</b><br>CF-BX-76-500                                                             |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |