

766nm CWL, 10nm FWHM, 11.8mm Unmounted Diameter



Bandpass Interference Filters

Stock **#43-092** CLEARANCE 3-4 DAYS

⊖ 1 ⊕ **€14,95**

ADD TO CART

Qty 1+

€14,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
11.80 ±0.15

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):
>9.2

Center Wavelength CWL (nm):
766.00

Center Wavelength CWL Tolerance (nm):

±2
Full Width-Half Max FWHM (nm): 10.00
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥50
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 5.10
Thickness Tolerance (mm): ±0.5
Type: Bandpass Filter
Typical Applications: K emission line
Blocking Wavelength Range (nm): 200 - 1200
Angle Sensitivity: Intended for Collimated Input

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View