

77L x 70mm Dia. Lens Tube, IP65/67

See More by [IDS Imaging Development Systems](#)



Stock **#19-686** **1 In Stock**

-

1

+

€146^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€146,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Camera Accessory

Type:

Note:

Accommodate C-Mount lens up to 68mm in length (without thread), 64mm in diameter

Regulatory Compliance

Compliant

RoHS 2015:

View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.