

TECHSPEC® 7mm, Uncoated, N-BK7 High Tolerance RA Prism



N-BK7 High Tolerance Right Angle Prisms

Stock **#32-541** ☐ In Stock

⊖

1

⊕

€82,00

ADD TO CART

Qty 1-5
€82,00

Qty 6+
€65,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (arcsec):
±15

Coating:
Uncoated

Substrate: ☐
N-BK7

Surface Quality: 40-20
Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 9.90
Length of Legs (mm): 7.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/8

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View