

(8-48mm FL), 6X Manual Zoom Video Lens



#53-152

Stock **#53-152** ☐ In Stock



1



€535,00

ADD TO CART

Qty 1+

€535,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
984 - 168

Length (mm):
97.00

Horizontal Field of View, 1/2" Sensor:
44.6° - 8.0°

Filter Thread:
M49.0 x0.75

Maximum Diameter (mm):

51.00
Weight (g): 305.00
Zoom Ratio: 6:1
Type: Zoom Lens, Macro
Focal Length FL (mm): 8.00 - 48
Maximum Sensor Format: 1/2"
Working Distance (mm): 1,200 - ∞
Mount: C-Mount
Aperture (f/#): f/1.2 - f/16
Lens Wavelength Range: VS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View

