

**TECHSPEC® 8" Diameter x 48" FL Uncoated, Parabolic Mirror**



Stock #32-074-000 3-4 DAYS

- 1 + **€843,00**

ADD TO CART

|         |
|---------|
| Qty 1-2 |
| €843,00 |

|         |
|---------|
| Qty 3+  |
| €717,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate:   
**BOROFLOAT®SUPREMAX®**

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:

|                                                     |
|-----------------------------------------------------|
| N/8                                                 |
| <b>Diameter (inches):</b><br>8.0 +0.06/-0           |
| <b>Diameter (mm):</b><br>203.20 +1.5/-0             |
| <b>Effective Focal Length EFL (inches):</b><br>48.0 |
| <b>Effective Focal Length EFL (mm):</b><br>1,219.20 |
| <b>Radius of Curvature (mm):</b><br>2,438.40        |
| <b>Aperture (f/#):</b><br>f/6                       |
| <b>Coating:</b><br>Uncoated                         |
| <b>Coating Type:</b><br>Uncoated                    |
| <b>Back Surface:</b><br>Ground                      |
| <b>Clear Aperture CA (mm):</b><br>183               |
| <b>Edge Thickness ET (inches):</b><br>1.37          |
| <b>Edge Thickness ET (mm):</b><br>34.80             |
| <b>Type:</b><br>Parabolic Mirror                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |