

80 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock #59-548 **4 In Stock**

- 1 + €328⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€328,00 each
Qty 5+	€312,30 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Pattern Location is Centered **Note:**

No **NIST Certification:**

Physical & Mechanical Properties

±0.100 **Dimensional Tolerance (inches):**

25.40	Length (mm):
12.7 x 25.4	Pattern Size (mm):
1.52 ±0.100	Thickness (mm):
76.20	Width (mm):
±0.001	Line Width Tolerance (µm):

Optical Properties

Vacuum Deposited Chrome	Coating:
80.00	Frequency (lp/mm):
Opal Glass	Substrate: <input type="checkbox"/>
>3.0	Optical Density OD (Average):
40-20	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance