

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Advanced Illumination Long Working Distance High Intensity Spot Lights

Stock #18-607 3-4 DAYS



1



€611,00

ADD TO CART

Qty 1+

€611,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
IR

Diameter (mm):
81.00

Input Voltage (V):
24V

Model Number:
SL246-940IC

Operating Temperature (°C): 0 - 60
Wavelength (nm): 940.00
Weight (g): 575
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant
Minimum Input Current: 0.40A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
