

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #36-625 3-4 DAYS



1



€197,00

ADD TO CART

Qty 1-4

€197,00

Qty 5+

€173,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.0

Maximum Aperture (mm):
60.0

Outer Diameter (mm):

82.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 8.0
Lever Length (mm): 11.00
Number of Leaves: 17
Thickness (mm): 10.10

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
