

85 x 50mm English Base Plate



Stock #58-998 **20+ In Stock**

⊖ 1 ⊕ €34⁵⁰

ADD TO CART

Volume Pricing

Qty 1+	€34,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

85.00 **Length (mm):**

50.00 **Width (mm):**

7.00 **Thickness (mm):**

Black Anodized Aluminum

Construction:

Number of Slots:

6

Threading & Mounting

Mounting Threads:

(4) 8-32, (5) 1/4-20

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 250:



Compliant

Product Details

- Two Size Options
- Two Platform Options: English or Metric
- English: Four #8-32 holes on 1/2" Square and Four 1/4-20 Holes on 1" Square
- Metric: Four M4 x 0.7 holes on 12.5mm Square and Four M6 x 1 Holes on 25mm Square
- Anodized Aluminum Construction

Base Plates have Metric or English threaded holes and additional center trapped hole (M6 x 1 or 1/4-20). Base Plates also have extended center slots that ensure full use on matching metric or English breadboard patterns. 85mm x 50mm Base Plates have same tapped holes and slots as 60mm x 35mm Base Plates, but with extra short slots for added flexibility.

Technical Information



Units: mm